

1230.40 1230 - 203 volt electronic soldering irons



- Range from 15W to 40W.
- High efficiency irons thanks to inside heating of the tip.
- Supplied with iron stand.

Spare tips:

- For iron 1230.25: pointy tip 1230.25P2
- For irons 1230.30 and 1230.40: pointed tip 1230.30P2 - screwdriver tip 1230.30P3

L [mm]: 240

No.: 420

Rating [W]: 40

Peak temp \pm 10% [°]: 420

Heating time [mn]: 2

Voltage\Volt: 230

[g]: 80