

FEATURES

- **Polyacrylic material:** Offers excellent resistance to chemicals and wear, ensuring long-lasting performance
- **Maximum operating pressure of 2000 kPa:** Suitable for high-pressure applications, providing robust sealing
- **Maximum operating temperature of 200 °C:** Capable of withstanding high temperatures, enhancing versatility
- **Rotary speed of 10 m/s:** Supports dynamic applications, maintaining efficiency in rotary equipment
- **Section size of 9.5 mm:** Ensures compatibility with a variety of gland sizes, offering flexibility

RS PRO 8m Polyacrylic Gland Packing, 2000 kPa

RS Stock No: 606-583



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO gland packing is designed for sealing applications in industrial environments. Made from durable polyacrylic material, it provides reliable sealing performance under high pressure and temperature conditions, making it ideal for use in pumps and valves.

General Specifications

Maximum Operating Pressure	2000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	10 m/s
Section	9.5 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Polyacrylic

Operation Environment Specifications

Maximum Operating Temperature	200 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------