

## Wall-Mount Monitor Arm - Full Motion - Articulating

Product ID: ARMPIVWALL



Free up valuable desk or table space by wall-mounting your flat-panel display (TV or computer monitor). This full-motion monitor arm supports monitors and TVs up to 30" and provides effortless height and viewing angle adjustments. You can tilt, swivel, and rotate your screen, making it easy to find the perfect viewing position.



## Save space by wall-mounting your flat-panel display

This sturdy mounting arm helps you save space on your desk or table surface, by letting you securely wall-mount a computer monitor or flat-screen TV, up to 30" in size. It's ideal for many different office applications, such as healthcare or financial settings, where you may want to share your display with patients, clients, or other visitors. The wall-mountable monitor arm also works well in office settings or workspaces that back against a wall.

You can also tuck your monitor in closely to the wall, to save more space while you're not working on your computer.

## Easy one-touch height adjustment

The monitor arm features a gas-spring cylinder, which makes it easy to raise or lower your display. You can also adjust the tension according to the weight of your monitor, so you can re-position the monitor height at any time, with one touch. Easy one-touch height adjustment makes the monitor arm ideal for shared workspaces with multiple alternating users, such as hotel meeting rooms or office boardrooms.

## Tilts and swivels to find the perfect viewing angle

The full-motion articulating arm makes it easy to find the right viewing angle. Just tilt or swivel your monitor to share your display, while collaborating with others. The articulating arm also supports a full 360-degree rotation, so it's easy to switch from landscape to portrait orientation, and back again.

## **Easy DIY installation**

The single-monitor arm makes wall-mounting your VESA compatible monitor fast and easy. It requires minimal assembly and features a built-in level, which helps you to position the arm assembly perfectly upright when mounting it to the wall. The mount also makes it easy to attach or remove your monitor with ease, and features built-in cable management to help keep your cables neat and tidy.

The ARMPIVWALL is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Free up desk or table space in business, commercial, industrial or office settings
- Share your monitor with clients, for easy collaboration in office settings such as healthcare, financial or real estate
- Ideal for shared workspaces with multiple users such as in hotel meeting rooms or office boardrooms
- Create space in home office settings

### Features

- Mount your monitor on a wall to save space
- Supports 12" to 30" flat-panel displays (LCD, LED and plasma TVs and computer monitors)
- Tucks in closely to the wall when not in use
- Full-motion, articulating arm lets you collaborate easily, by adjusting your monitor's viewing angle to share with others
- One-touch height adjustment with gas-spring arm
- Easy monitor attachment and removal
- Simple DIY installation with built-in level

<b>Hardware</b>	Warranty	2 Years
	# of Displays Supported	1
	Articulating	Yes
	Cable Management	Yes
	Mounting Options	Wall-Mount
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
	Wallmountable	Yes
<b>Performance</b>	Built-in Level	Yes
	Display Rotation	360°
	Maximum Arm Extension	24.4 in [620 mm]
	Maximum Display Size	30in
	Maximum Height	11.8 in [300 mm]
	Pan	180°
	Tilt	+90° / -65°
	Weight Capacity (Per Display)	19.9 lb [9 kg]
<b>Physical Characteristics</b>	Color	Black
	Product Height	4.3 in [108 mm]
	Product Length	24.4 in [620 mm]
	Product Weight	4.3 lb [2 kg]
	Product Width	4.5 in [115 mm]
<b>Packaging Information</b>	Package Height	5.8 in [148 mm]
	Package Length	18.6 in [472 mm]
	Package Width	8 in [204 mm]
	Shipping (Package) Weight	5.5 lb [2.5 kg]
<b>What's in the Box</b>	Included in Package	1 - spring arm 1 - cover 1 - wall plate 1 - M5 Allen key 1 - M6 screw

2 - 6.3 x 65 mm screws

4 - M4x12 mm screws

4 - M4x25 mm screws

2 - anchors

2 - washers

4 - spacers

1 - zip tie

1 - instruction manual

---

Product appearance and specifications are subject to change without notice.