

PSD-4; 0...10 bar gauge ; two switching outputs (PNP/NPN)

PSD-4; 0...10 bar gauge ; two switching outputs (PNP/NPN)

Item number: 14240418

Quantity: 1 pcs.

Order code: PSD-4-9Z-BG410-HD1Z-WW-ZZ

W1011PS4Z-SZAB-P-GSFI

Overview: PSD-4; 0...10 bar gauge ; two switching outputs (PNP/NPN)

Electronic pressure switch with display

Output signal: two switching outputs (PNP/NPN)

IO-Link: without

Power supply: 15...35 V DC

Measuring range: 0...10 bar gauge

Process connection: G 1/4 A DIN EN ISO 1179-2

Sealing: NBR

Media temperature: -20 ... 85 °C (-4 ... +185 °F)

El. connection: Circular connector M12x1 (4-pin)

pin assignment el. connection: U+=1, U-=3, SP1=4, SP2=2

Accuracy: $\pm 0.5\%$ of span

Approvals: cULus

with test protocol

Specifications according to data sheet: PE 81.86

Details: PSD-4; 0...10 bar gauge ; two switching outputs (PNP/NPN)

Electronic pressure switch with display

Output signal: two switching outputs (PNP/NPN)

IO-Link: without

Power supply: 15...35 V DC

Measuring range: 0...10 bar gauge

Process connection: G 1/4 A DIN EN ISO 1179-2

Sealing: NBR

Media temperature: -20 ... 85 °C (-4 ... +185 °F)

El. connection: Circular connector M12x1 (4-pin)

pin assignment el. connection: U+=1, U-=3, SP1=4, SP2=2

Accuracy: $\pm 0.5\%$ of span

Approvals: cULus

with test protocol

Specifications according to data sheet: PE 81.86