

Han 1A-strain relief

Part number	09 10 000 5300
Specification	Han 1A-strain relief
HARTING eCatalogue	https://b2b.harting.com/09100005300

Identification

Category	Accessories
Series	Han [®] 1 A
Type of accessory	Strain relief

Version

Cable tie is included within the delivery

Technical characteristics

Limiting temperature	-30 +90 °C
Number of relockings	<10
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (accessories)	Polyamide
Colour (accessories)	Black
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	EN 45545-2 R22: HL1, HL2, HL3 EN 45545-2 R23: HL1, HL2, HL3 EN 45545-2 R24: HL1, HL2, HL3 EN 61373 Cat 1B
Commercial data	
Packaging size	1

Page 1 / 2 | Creation date 2019-04-12 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com Product data sheet 09 10 000 5300 Han 1A-strain relief



Commercial data

Net weight

Country of origin

5 g

Germany

European customs tariff number

85366990

eCl@ss

27440392 Connector (accessories)