



General characteristics

Diameter	mm - inch	50 / 1.97
Material		Metal


Mechanical features

Weight	g	27
--------	---	----

Ambient conditions

Temperature	Operating temperature	
	min	°C -30
	max	°C +50

Dimensions



Type	L (mm/in)
LTP50P050T	50 (1.97")
LTP50P100T	100 (3.94")
LTP50P250T	250 (9.84")
LTP50P400T	400 (15.75")

Certifications and compliance

Compliance

CSA C22.2 n° 14
IEC/EN/BS 60947-1
IEC/EN/BS 60947-5-1
UL508

Certificates

cULus

ETIM classification

ETIM 8.0	EC001155 - Tube for signal tower
----------	--