



RCBO 1P+N 4.5kA C-16A 30mA AC Class

ADC816F

Technical Properties

Type of pole	1P+N
Curve	C
Rated short circuit breaking capacity	4.5 kA
Rated current	16 A
Rated operational voltage Ue	240 V
Number of modules	2
Connection cross-sect. flexible cable	1,5 bis 95mm ²
Connection cross-sect. rigid cable	1,5 to 95mm ²
Rated short circuit breaking capacity 230V 50Hz	4.5 kA
Tightening torque	10Nm
European directive RoHs	voluntary compliance
European directive WEEE	not concerned