

FEATURES

- **Concealed design:** Provides a clean and unobtrusive appearance
- **304 stainless steel construction:** Offers high corrosion resistance and durability
- **Removable pin:** Facilitates easy installation and maintenance
- **Bolt-On/Rivet fixing method:** Ensures secure attachment
- **Two holes per leaf:** Simplifies alignment and installation

RS PRO 60 mm Concealed Hinge, 304 Stainless Steel

RS Stock No: 335-177



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price

Product Description

This RS PRO concealed hinge is designed for applications requiring a sleek, hidden hinge solution. Made from durable 304 stainless steel, it offers excellent corrosion resistance, making it ideal for both indoor and outdoor use. The hinge features a removable pin, allowing for easy installation and maintenance.

General Specifications

Fixing Method	Bolt-On/Rivet
Hinge Type	Concealed
Holes per Leaf	2
Pin Style	Removable Pin
Product Type	Concealed Hinge

Mechanical Specifications

Length	60 mm
Material	304 Stainless Steel
Thickness	24.5 mm
Width	42 mm

Approvals

Standards/Approvals	REACH, RoHS
---------------------	-------------