

CET11-287x287x292-0P



Application:EPA-filter for standard applications

Type:EPA-filter

Frame:Electro Zink sheet

Gasket:Polyurethane

Media:Glass fibre

Separators:Hot melt beads

Sealant:Polyurethane

Efficiency according to EN 1822:E11

MPPS efficiency:≥95% MPPS

Temperature/Humidity:70°C/100% RH maximum in continuous service

Remarks:All filters scan tested, document supplied in the box

Article number	Type	Size	Area (m ²)	Air flow (m ³ /h)	Pressure drop (Pa)
CCCONEPA	ABSOLUTE C /CamCleaner Concealed	CET11-287x287x292-0P	5	400	109

