

# TECHNICAL DATA SHEET

## US-45 All-purpose Spray

### Description

US-45 can be used as a multipurpose product with lubricating, rust dissolving, protecting and moisture repellent properties. It can be used on all types of machinery.

US-45 cleans, protects and lubricates all kinds of metal parts and is safe to use on most surfaces including plastic and rubber.

Fastacting rustdissolver - is ideal for the dismantling of rust bounded nuts, bolts, valves etc.

US-45 is a high performance penetrating lubricant, that leaves a light lubricating oil film. The product protects wires, brake parts, gearwheels, locks, tools etc.

US-45 is a low viscosity lubricant which is invaluable for penetrating and lubricating inaccessible areas.

US-45 has excellent moisture repellent properties and is safe to use on batteries, starters and cables.

Protects all metal parts exposed to moisture and water. Re-establish contact. Start problems and leak current are avoided.

Excellent corrosion protecting properties that leave a protecting film for short-term, indoor storage. The product cleans tarnished and lusterless metals and prevents additional listlessness. US-45 removes dirt, soot, grease, tar and film. US-45 is silicone- and resin-free and will not create accumulation.

### Properties

- lubricating/penetrating, cleaning
- rust dissolving, moisture repellent
- re-establish contact
- corrosion inhibiting
- removes unpleasant sounds
- no deteriorating effect on plastic/rubber
- cleaning effect





# TECHNICAL DATA SHEET

## US-45 All-purpose Spray

### Technical and physical data

Partnumber	18452	18455
Packing	spraycan 200ml	spraycan 500ml
Weight		368 g
Propellant	propane/butane	
Colour	clear/transparent	
Odour	mild/fresh	
Base	hydrocarbons	
Density at 15°C	0,71 g/cm <sup>3</sup>	
Watersoluble	<0,30 weight%	
Temperature from	-25°C to	
Valve	Replaceable	
Flashpoint	57°C	
Emptying rate	0,796 g/sec.	