

70648

UST Deck Scrub, 400 mm, Hard, Purple



This ULTRA SAFE TECHNOLOGY (UST) Deck Scrub comes with angled Filament Security Units for effective removal of stubborn dirt from both textured and smooth surfaces in high-risk areas. All UST brushes feature a unique bristle system that minimises the risk of contamination and bristle loss.

Technical Data

| | |
|---|--|
| Item Number | 70648 |
| Visible bristle length | 37 mm |
| Material | Polyester Glass reinforced Polypropylene |
| Complies with (EC) 1935/2004 on food contact materials ¹ | Yes |
| Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice | Yes |
| FDA compliant raw material (CFR 21) | Yes |
| Meets the REACH Regulation (EC) No. 1907/2006 | Yes |
| Use of Phthalates | No |
| Is Halal compliant | Yes |
| Patent Pend. No. | PA201270087, PA201270088 |
| Box Quantity | 10 Pcs. |
| Quantity per Pallet (80 x 120 x 200 cm) | 480 Pcs. |
| Quantity Per Layer (Pallet) | 1 Pcs. |
| Box Length | 410 mm |
| Box Width | 290 mm |
| Box Height | 200 mm |
| Length/Depth | 400 mm |
| Width | 50 mm |
| Height | 75 mm |
| Gross Weight | 0,38 kg |
| Net Weight | 0,35 kg |
| Cubik metre | 0,0019 M3 |
| Max. usage temperature (for food contact) | 80 °C |
| Max usage temperature (non food contact) | 80 °C |
| Recommended sterilisation temperature (Autoclave) | 121 °C |
| Max. cleaning temperature (Dishwasher) | 93 °C |
| Max. drying temperature | 100 °C |
| Min. usage temperature ³ | -20 °C |
| Max. pH-value in Usage Concentration | 10,5 pH |
| Min. pH-value in usage concentration | 2 pH |
| Recycling Symbol "7", Miscellaneous Plastics | Yes |
| GTIN-13 Number | 5705020706486 |
| GTIN-14 Number (Box quantity) | 15705020706483 |
| Commodity Code | 96039099 |

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

3. Do not store the product below 0° Celsius.