





3 Way Electrically Actuated Stainless Steel Ball Valve 'L' Bore

1000 PSI Rated


Article no. L bore	Size	Actuator Size
RS399063	1/2"	HQ003
RS399064	3/4"	HQ003
RS399065	1"	HQ003

Materials

Body CF8M - 316 Stainless Steel

Ball 316 Stainless Steel

Stem Seal PTFE
Ball Seal PTFE
Temp. Range +70°C*



Specifications - HQ003 Actuator

Enclosure Rated Weather proof IP67
Motor 24V DC Motor

Supplying Voltage Multi-Voltage(85~265VAC or 24VDC)
Limit Switches 2 x open/close SPDT, 250 VAC 6A rating
Auxiliary Limit Switches 2 x open/close SPDT, 250 VAC 6A rating

Torque Switch N/A
Travel Angle 90 degree


Indicator LED lamp Indicator(Open/Close)
Heater N/A

Manual Override Push Button with Manual lever
Conduit Entries 1 X PG11 with 3m flying lead. 11 wires

Ambient Temperature -20 ~ + 60

External Coating Polyester Powder Coating

Base and Bore ISO5211(F03/04/05) & 11mm Double Square



То	Max.	R	Rated Current		Electric	Operating	Bore	Base
	Torque (Nm)	110VAC	220VAC	24VDC	Motor Stop	time	Size	(ISO5211)
HQ-003	30	0.12A	0.06A	0.46A	2.0A	12sec	11mm Star	F03/04/05

Overall Dimensions

Dia Size ins.	Α	D	E	F	ØМ
1/2"	72	42	61.46	36	11
3/4"	83	46.5	73.63	41.5	16
1"	110	55	84.30	55	20

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.