

111EN

Adjustable wrenches with scales, phosphated

DIN 3117 ISO 6787

The new adjustable wrench with scale, Beta 111EN, allows differently sized nuts and bolts to be tightened and loosened through the sliding jaw, which can be adjusted through the central roll.

Features:

- Head angled at 15 degrees, allowing hardly accessible spaces to be reached
- New ergonomic properties resulting in 20% weight reduction
- Wide wrench opening
- Compact head with completely open jaw
- Left-hand rotation
- Double laser marking in mm/inches
- Matt chrome-plated heads for improved scale readout
- Matt chrome-plated body
- Made from high-performance alloy steel for increased mechanical torsional strength
- Special heat treatment for excellent wear resistance
- Large handle for optimized comfort
- Hole on handle for hanging wrench
- Complies with DIN 3117 - ISO 6787

Lightweight

Compact

Ergonomic



	art.			A max mm	
001110410	111EN 100	100	4	15	50
001110415	111EN 150	150	6	24	145
001110420	111EN 200	200	8	29	265
001110425	111EN 250	250	10	34	387
001110430	111EN 300	300	12	40	685
001110438	111EN 380	380	15	45	1170
001110445	111EN 450	450	18	54	1780