



Product number 1656005012
EAN 4007123632343

DESCRIPTION

- Robust extension sockets, designed to be the best and made of break-resistant special plastic material.
- Earthed sockets in a 45° arrangement, ideal for angular plugs.
- Illuminated 2-pole ON/OFF safety switch.
- With option to wind the cable around the rail for storage.
- With practical hanging facility.
- Socket with increased touch protection.

TECHNICAL DATA

Cable quality	PVC	Max. current carrying capacity	10 A
Product number	1656005012	USB type output socket	Not applicable
Cable length	3 m	With surge protection	No
Cable designation	H05VV-F 3G1,5	With interference suppressor filter	No
Socket outlets switchable	12	Colour	black
Socket outlets total	12		

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	1.1 kg
Weight of product (without packaging)	1.09 kg	Dimension LxWxH (incl. packing)	5.5 cm x 9 cm x 77 cm