



Capacities from 4.5 to 50 tonnes

Stroke lengths from 10 to 150 mm





Working pressure 700 bar

- ▶ Choice of pump and cylinder sets with accessories included
- ▶ Single acting, spring assisted return cylinders with solid or hollow pistons
- ▶ Manually operated lightweight aluminium pumps with factory set safety relief valve
- ▶ Standard 2 metres length hose with quick connect couplers


OEM SET		CYLINDER	PUMP	ACCESSORIES INCLUDED				Couplers & Fittings
Part number	Model number	Model number	Hose	Gauge	Gauge block	Box		
OEM/003/001	HSS55	HP211	HC2	HG1	HGA2	-	-	
OEM/003/002	HSS102	HP212	HC2	HG10	HGA2	-	-	
OEM/003/003	HSS106	HP212	HC2	HG10	HGA2	-	-	
OEM/003/004	HSS154	HP212	HC2	HG1	HGA2	-	-	
OEM/003/005	HSS156	HP212	HC2	HG1	HGA2	-	-	
OEM/003/006	HSS256	HP212	HC2	HG25	HGA2	-	-	
OEM/003/007	HLS101	HP212	HC2	HG10	HGA2	-	-	
OEM/003/008	HLS201	HP212	HC2	HG20	HGA2	-	-	
OEM/003/009	HLS302	HP212	HC2	HG32	HGA2	-	-	
OEM/003/010	HHS101	HP212	HC2	HG11	HGA2	-	-	
OEM/003/011	HHS202	HP212	HC2	HG63G	HGA2-25	-	-	
OEM/003/012	HHS302	HP212	HC2	HG63G	HGA2-25	-	-	
OEM/003/013	HSS106	HP212	HC2	HG10	HGA2	MSB2	-	
OEM/003/014	HSS154	HP212	HC2	HG1	HGA2	MSB2	-	
OEM/003/015	HSS156	HP212	HC2	HG1	HGA2	MSB2	-	
OEM/003/016	HLS101	HP212	HC2	HG10	HGA2	MSB2	-	
OEM/003/017	HLS201	HP212	HC2	HG20	HGA2	MSB2	-	
OEM/003/018	HPS100	HP212	HC2	HG10	HGA2	MSB2	-	
OEM/003/019	HPS500	HP212	HC2	HG50	HGA2	MSB2	-	
OEM/003/020	-	-	-	HG63G	AGA1-25	-	CF1, PPC1	

Note: For more details on the cylinders, pumps and accessories included in the OEM kits, please refer to the tables on Page 2






1. CYLINDERS

Range	Model number	Capacity (tonnes)	Stroke (mm)	Closed height (mm)
 <p>HSS Range Single Acting Multi-purpose Cylinders</p>	HSS55	4.5	125	207
	HSS102	10	56	131
	HSS106	10	150	225
	HSS154	14.5	100	204
	HSS156	14.5	150	254
	HSS256	25	150	273
 <p>HLS Range Single Acting Low Height Cylinders</p>	HLS101	10	40	95
	HLS201	20	44	102
	HLS302	32	60	119
 <p>HHS Range Single Acting Hollow Piston Cylinders</p>	HHS101	11	25	110
	HHS202	23	50	160
	HHS302	33	50	165
 <p>HPS Range Single Acting Low Height Pad Cylinders</p>	HPS100	10	10	46
	HPS500	50	15	67

2. PUMPS

Range	Model number	Valve type	Oil capacity (litres)
 <p>HP Range - Aluminium Manually Operated Aluminium Pumps</p>	HP211	2-way	0.5
	HP212	2-way	1

3. ACCESSORIES

Range	Model number
 <p>Hydraulic Hoses High pressure 2 metre hydraulic hoses</p>	HC2
 <p>Pressure Gauges Dry or glycerine-filled gauges to monitor hydraulic pressure</p>	HG1
	HG10
	HG11
	HG20
	HG25
	HG32
	HG50
 <p>Gauge Mounting Blocks For easy "inline" connection of the pressure gauge to the hydraulic system</p>	HG63G
	HGA2
	HGA2-25
 <p>Tool Boxes Durable metal storage and transport boxes</p>	AGA1-25
	MSB2
 <p>Couplers & Fittings Designed to ensure easy system connection and assembly</p>	CF1, PPC1