



Product data sheet

Power tools for trade & industry

Cordless Circular Saw

PRO GKS 18V-51



Move freely with effortless cuts.

The most important data

Battery voltage	18.0 V
Saw blade diameter	140 mm
No-load speed	5,800 – 6,300 rpm

Part Number 0 601 9M3 120

Technical data

Technical data

No-load speed	5,800 – 6,300 rpm
Saw blade diameter	140 mm
Saw blade bore diameter	20 mm
Weight excl. battery	2.2 kg
Battery voltage	18.0 V
Packaging dimensions (width x length x height)	197 x 375 x 18 mm
BITURBO	No

Noise/vibration information

Wood sawing

Vibration emission value ah	2 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Provides effortless cutting with the 18V brushless motor
- Easy to carry and comfortable to use thanks to the compact design and ergonomic handle
- Keeps dust away due to the better dust extraction port design
- Smooth starting and stopping with optimized soft start and brake functions
- Cutting line always in clear view thanks to dust blower function
- Lights up even awkward corners with LED light



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

