



Main

| | |
|---------------------------|---|
| Range of product | Acti 9 |
| Modular device name | IHP |
| Device short name | IHP 1c |
| Product or component type | Programmable digital time switch |
| Product compatibility | Mechanical compatibility with electrical distribution comb busbars |
| Number of channels | 1 |
| Battery type | Lithium |
| Function available | Automatic time changeover |
| Type of setting | Absence for holidays function |
| Language | Danish Dutch English Finnish French Norwegian Swedish |

Complementary

| | |
|--------------------------------|--|
| Device application | Building |
| Measurement accuracy | +/- 1 s/day |
| Cycle duration | 24 hours + 7 days |
| Maximum number of switchings | 56 |
| Minimum interval duration | 1 min |
| Measurement accuracy | +/- 1 s/day 20 °C |
| Power consumption | 4 VA |
| Maximum switching current | 16 A - 250 V AC pf = 1 10 A - 250 V AC pf = 0.6 |
| [Ue] rated operational voltage | 230 V (+/- 10 %) AC 50/60 Hz |
| Display type | Backlit LCD |
| Battery life | 6 yr |
| Backup time | 6 years time and program saving |
| Product mounting | DIN rail |
| 9 mm pitches | 5 |
| Colour tint | White(RAL 9003) |
| Width | 45 mm |
| Height | 85 mm |
| Depth | 66 mm |

Environment

| | |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -10...50 °C |
| IP degree of protection | IP20 B |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

| | |
|----------------------------------|--|
| Sustainable offer status | Green Premium product |
| RoHS | Compliant - since 0946 - Schneider Electric declaration of conformity |
| REACH | Reference contains SVHC above the threshold - go to CaP for more details |
| Product environmental profile | Available Download Product Environmental |
| Product end of life instructions | Available Download End Of Life Manual |

Contractual warranty

| | |
|--------|-----------|
| Period | 18 months |
|--------|-----------|