

Eaton 24FDIHA16

Catalog Number: 24FDIHA16

Fuse-link, medium voltage, 16 A, AC 22 kV, 51 x 565 mm, full-range, BS, with striker

General specifications



Product Name	Catalog Number
Eaton Bussmann series medium voltage BS air fuse	24FDIHA16 EAN 5027590468909
Product Length/Depth	Product Height
590 mm	50.8 mm
Product Width	Product Weight
50.8 mm	2731.667 g
Certifications	
BS 2692-1	

Product specifications

Resources

Used with

A3354710 Fuse clip

Type

fuse

Application

protection of primary side
transformers
used in fuse switch
combination units, fuse
bases and fuse switches

Amperage Rating

16 A

Fuse size

50.8 x 565 mm

Breaking capacity

35.5 kA

Installation technique

Air

Performance Cat According To IEC 60282-1

Full-range

Product application

Primary side transformer protection

Rated frequency - max

50 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

British Standard

Utilization category

Other

Voltage type

AC

With striker

Yes

Class

Class full-range

Fuse shape

Cylindrical

Pre arc (I₂T)

1.1 x 103

Resistance

103 ohms

Fuse diameter

51 mm

Interrupt rating

35.5 kAIC

Construction size

51 x 565 mm

Mounting method

Clip-in

Voltage rating

24 kV

Fuse type

FDIH



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia