



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-111623-9
14, 2MM, POL,30 DP, LEAD FREE



TE Part # 1-111626-8
14, 2MM, 30 DP, LEAD FREE



Customers Also Bought

TE Part #5-1879255-5
RP 2B 78R7 0.1% 15PPM CUT LENGTH

TE Part #4-640433-0
10P MTA156 CONN ASSY 22AWG RED

TE Part #1744048-7
07P EC PWR.200 CL HDR ASSY RA

TE Part #2213678-4
Z35 MINI LED HOLDER 12*15MM
COUNTERSUNC

TE Part #3-1879353-0
RR02 5% 68K AMMO

TE Part #T4052224003-001
RPC-M8-3MR-0.5-M8-3FR-PUR

TE Part #5-1879127-2
RN 0402 374R 0.1% 10PPM CUT
LENGTH

TE Part #CG3322-000
CI-TM60050

TE Part #1879129-5
RN 0402 1K24 0.1% 10PPM 1K RL

TE Part #5767056-5
MICT,260,PLUG,190,ASSY,PDNI

Documents

Product Drawings

14 AMPMODU 2MM, H, AU, LF

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5176837-6_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5176837-6_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5176837-6_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

AMPMODU_INTERCONNECTION_SYSTEM_SECTION3AND4

English