

# ASCM 18 QM

4-speed cordless drill/driver

Order number:: 7 116 11 61 00 0



4-speed cordless drill/driver with brushless motor and QuickIN MAX interface. No compromise on performance for drilling and tapping up to 12 mm and drilling with carbide hole saws.

- Brushless FEIN PowerDrive motor, fully encapsulated and dust-protected with 30% higher efficiency and long service life.
- 4-speed solid metal gearbox. Optimum cutting speeds for drilling in metal and self-drilling screwdriving.
- QuickIN MAX accessory interface for all QuickIN and QuickIN MAX accessories. Quick change between applications.
- High torques up to 90 Nm.
- Including QuickIN solid metal drill chuck (120 Nm) with carbide-tipped clamping jaws and high clamping forces.
- In speed 4, optimum speeds (3850 rpm) for small diameters.
- In speed 3, optimum speeds (1950 rpm) for 8 mm diameters.
- Speed 1 for powerful thread cutting.
- Suitable for carbide hole saws up to 25 mm.
- Electronic torque setting.
- Fixes 10 x 400 mm screws without pre-drilling.
- 2200 screw connections (5x40 mm) with one battery charge (5 Ah).
- One charger for all FEIN Li-ion batteries of all voltage classes.
- The battery charge can be read off the battery.
- FEIN SafetyCell technology. Protects the battery and tool from overload, overheating and total discharge.
- 3-year FEIN PLUS warranty including battery and charger.



# ASCM 18 QM

4-speed cordless drill/driver

Order number:: 7 116 11 61 00 0

## Technical data

---

Battery voltage	18 V
Battery capacity	5 Ah
Motor	brushless
Gearbox	4-speed
Interface	QuickIN MAX
Speed, no load	400 / 800 / 1 950 / 3 850 rpm
Max. torque (hard/soft)	90 / 45 Nm
Torque levels	15 + 1
Drill chuck clamping width	1,5 - 13 mm
Fastening	10 x 400 mm
Capacity in steel Ø	25 mm
Capacity in wood Ø	50 mm
Tapping	M 12
Weight with battery	2,20 kg
Weight without battery	1,50 kg
Cordless	X

## Included in price::

---

1 cordless drill/driver
2 battery packs (Li-ion)
1 rapid charger ALG 50
1 QuickIN drill chuck (120 Nm)
1 belt clip
1 bit holder
1 handle
1 plastic carrying case