

**1696B**

**spirit levels with magnetic bases made from anodized profiled aluminium, 2 unbreakable vials accuracy: 1 mm/m**

- Precision 1 mm/m

|  | art.      | L<br>mm | H<br>mm | S<br>mm | g   |
|---------------------------------------------------------------------------------|-----------|---------|---------|---------|-----|
| <b>016960202</b>                                                                | 1696B 200 | 200     | 49      | 22      |     |
| <b>016960203</b>                                                                | 1696B 300 | 300     | 49      | 22      | 225 |
| <b>016960204</b>                                                                | 1696B 400 | 400     | 49      | 22      | 275 |
| <b>016960205</b>                                                                | 1696B 500 | 500     | 49      | 22      | 340 |
| <b>016960206</b>                                                                | 1696B 600 | 600     | 49      | 22      | 375 |

