



ENGLISH

Datasheet

**RS Pro Cartridge Fuse, T, 8A**

RS Stock No: **610-9838**



## Product Details

RS Pro cartridge fuse is current rated for 8 A. This time delay fuse has ceramic body, T-speed and nickel plated brass ends.

**Specifications:**

Body Material	Ceramic
Breaking Capacity (at Maximum Voltage Rating)	1500 A
Current Rating	8 A
Diameter	5.2 mm
Fuse Speed	T
High Rupture Capacity	Yes
Includes Indicator	No
Maximum Operating Temperature	+85°C
Minimum Operating Temperature	-40°C
Operating Temperature Range	-40 to +85°C
Overall Dimensions	5.2 x 20 mm
Overall Length	20 mm
Size Designation	Miniature
Voltage Rating	250 V
Standards Met	UL, VDE, BSI, EN 60127/V and IEC 127-2/V, RoHS Compliant