



## Pliers Wrench Gripper

- | The universal pliers wrench for gripping nuts and refined fittings
- | Replaces a whole range of metric and imperial spanners
- | For careful mounting, e.g. of fittings with surface refinement
- | For tightening and loosening bolted connections according to the ratchet principle
- | Smooth inside jaws
- | Parallel gripping jaws ideally suited to gripping, holding, pressing and bending a wide range of workpieces, e.g. as a tile nibbler, for locknuts or as a small vice
- | High clamping force due to sophisticated lever design that multiplies the force applied by the hand
- | Push-button adjustment with fine serration for quick and secure adaptation to the workpiece to be gripped
- | Box joint with wide guide surfaces
- | Micro-grinding for easy adjustment
- | Finger trap protection for safe work, prevents injuries caused by squeezing
- | Ergonomic handle position and shape for optimum power transmission
- | Handles coated with plastic
- | Made of special tool steel, forged, oil-hardened

SKU: 1664-12-250-SB

### General Information

#### Fittings Pliers

s wrenches are oil hardened and tempered to exacting standards and have been developed specifically for the task of fitting sanitary fittings carefully and gently. The swivelling jaws will get a good grip in any position and ensure optimum pressing force for work on fittings of all kinds. The all-round helper is not only suitable for tightening and loosening screw joints – in particular the nuts on fittings with high-grade coatings – they can also be used as tile nibblers as a result of their smooth, polished gripping surfaces.



## Prepared for anything

For many heating engineers and plumbers, the exception proves to be the rule – for example, when they are called to deal with burst water pipes. They do not know in advance what to expect. But with the right selection of versatile tools, every problem becomes a routine task. The NWS tool compilation provides the plumber with tools that are just right and durable for every occasion. And if they need to get to grips with large-diameter pipes, they can do just that with the ClassicPlus.

## Downloads

	1664-12-250.jpg		detail_1664-12-250_2108261649.jpg		detail_1664-12-250_2109031814.jpg
	detail_1664-12-250_2109071750.jpg		detail_1664-12-250_2109071745.jpg		detail_1664-12-250_2109071743.jpg
	detail_1664-12-250_2109100916.jpg				

## Technical Data

1664-12-250-SB		
◀▶	Length - mm	250
◀▶	Length - in	10

	Wrench size - mm	50
	Spannweite - mm	52
	Span - in	2
	DIN standards - National, European and worldwide	DIN ISO 5743
	Weight - g	420
	Length including self-service packaging - mm	295
	Width including self-service packaging - mm	65
	Height including self-service packaging - mm	16
	Weight self-service packaging - g	10
	Packing unit	6
	Barcode	40 03758 66645 6