

Datasheet

RS Pro Non-Fused Terminal Block, 2 Way/Pole, Screw Terminals, 2 x 16 mm², PC, 450 V

RS Stock No: **868-0764**



Product Details

RS Pro non-fused terminal block with 2-way, has blue transparent polycarbonate housing. This terminal block with 2 x 16 mm² wire, features screw termination. The panel mount block with brass contact, has a voltage rating of 450 V. This terminal block meets EN 60998-1: 2004 and CEI 23-21 - II Ed. (EN 60998-2-1) + V1 standards.

Features and Benefits

- Self-extinguishing of UL 94-V0, IEC 695-2-1 to 850°C
- Maximum operating temperature of 85°C
- Brass clamps
- galvanised steel screws

Specifications:

Contact Material	Brass
Enclosed	Yes
Material	PC Housing
Maximum Operating Temperature	+85°C
Mounting Type	Panel Mount
Number of Ways	2
Termination Method	Screw
Voltage Rating	450 V
Wire Size	2 x 16 mm ²
Colour	Transparent Blue
Standards Met	RoHS, UL 94V-0, IEC 695-2-1, EN 60998-1:2004, CEI 23-21 - II Ed. (EN 60998-2-1) + V1