

ML10/13.SFD



Products Low Voltage Products and Systems Connection Devices Terminal Blocks SNA Series

General Information

Extended Product Type:	ML10/13.SFD
Product ID:	1SNA199166R2600
EAN:	3472591991666
Catalog Description:	ML10/13.SFD Screw Clamp Terminal Blocks - For 6.3 x 25 and 6.3 x 32 fuses - with blown fuse indicator by Neon 480V - Black
Long Description:	- Protect your circuits with 6.35x25.4 and 6.35x32 fuse terminal blocks (fuse not supplied with terminal blocks), - Quickly identify the defective circuit thanks to the blown fuse indicator.

Additional Information

ABB Industrial IT Suite:	Control IT
CSA Certificate:	1SND161066A0201
Color:	Black
Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Rigid 1x 22 ... 10 AWG
Connecting Capacity UL/CSA:	Screw Clamp / Rigid 22 ... 10 AWG Stranded 10 AWG
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.5 ... 10 mm ² Screw Clamp / Rigid 1x 0.5 ... 16 mm ²
Connection Type:	Screw clamp
Country of Origin:	France (FR)
Customs Tariff Number:	85361050
Data Sheet, Technical Information:	1SNC160019C0202
Declaration of Conformity - CE:	1SND225016U1000
EAC Certificate:	1SND161009A1100
EAN:	3472591991666
ETIM 4:	EC000899 - Fuse terminal block
ETIM 5:	EC000899 - Fuse terminal block
ETIM 6:	EC000899 - Fuse terminal block
Environmental Information:	1SND220021E1002
Flammability According to UL94:	V0
Function:	Fuse
Gauge Type:	A6
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNC160019C0202
Invoice Description:	ML10/13.SFD Screw Clamp Terminal Blocks - For 6.3 x 25 and 6.3 x 32 fuses - with blown fuse indicator by Neon 480V - Black
Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Minimum Order Quantity:	20 piece
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Connections:	2
Number of Levels:	1
Object Classification Code:	X
Order Multiple:	20 piece
Package Level 1 EAN:	3472591991666
Package Level 1 Gross Weight:	1.08 kg

Package Level 1 Gross Weight:	1.00 kg
Package Level 1 Height:	71 mm
Package Level 1 Length:	155 mm
Package Level 1 Units:	20 piece
Package Level 1 Width:	172 mm
Package Level 2 Gross Weight:	11.300 kg
Package Level 2 Height:	300 mm
Package Level 2 Length:	500 mm
Package Level 2 Units:	200 piece
Package Level 2 Width:	300 mm
Package Level 3 Units:	4800 piece
Pollution Degree:	3
Product Main Type:	ML10/13.SF
Product Name:	Terminal block
Product Net Depth:	58 mm
Product Net Height:	85 mm
Product Net Weight:	54 g
Product Net Width:	13 mm
Product Packing Type:	Box
RMRS Certificate:	1SND161007A1101
Rated Cross-Section:	10 mm²
Rated Current (I _n):	Main Circuit 10 A
Rated Impulse Withstand Voltage (U _{imp}):	8000 V
Rated Voltage (U _r):	800 V
Recommended Screw Driver:	5.5 mm
RoHS Date:	20050518
RoHS Information:	1SND230023F0208
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Selling Unit of Measure:	piece
Short Description:	black Screw Clamp Terminal Blocks ML10/13.SFD with LED blown fuse indicator
Spacing:	13 mm
Sub-Function:	For 6.3x25 and 6.3x32 Fuses
Sub-Function 2:	With blown fuse indicator by LED 24V
Sub-Function 3:	For 6.3x25 and 6.3x32 Fuses
Sub-Function 4:	With blown fuse indicator LED
Tightening Torque:	acc. IEC 60947-1 1.2 N·m Manufacturer 1.4 N·m
Wire Stripping Length:	12.0 mm
cUL Certificate:	1SND161000A0203
Number of Potentials:	1



