



Product data sheet

Power tools for trade & industry

HWS 5265/125

INDUSTRIAL HWS 5265/125

For light-duty grinding work

The most important data

Permitted sanding disc diameter	125 mm
No-load speed	5,800 rpm
Rated power, output	360 W

Part Number 0 602 324 444



Technical data

Technical data

Frequency	200 Hz
Voltage	135 V
Permitted sanding disc diameter	125 mm
No-load speed	5,800 rpm
Rated power, input	520 W
Rated power, output	360 W
Rated current	3.2 A
Weight as per EPTA	2.5 kg
Toolholder, drive end	M14
Switch version	Slide switch

Product data sheet

Power tools for trade & industry



BOSCH
Invented for life

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

