

2U Vented Sliding Rack Shelf w/ Cable Management Arm & Adjustable Mounting Depth - 50lbs / 22.7kg

**Product ID:** UNISLDSHF192



The UNISLDSHF192 Adjustable Sliding Rack Shelf lets you add a vented, sliding shelf with cable management into virtually any 4-post server rack or cabinet. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The adjustable mounting depth design allows the shelf to be installed easily into server cabinets with mounting depths from 27.7in (702.2mm) to 31.6in (802.2mm). The sliding rails also offer a locking mechanism to stop the shelf from sliding out too far, or sliding back into the rack before maintenance is complete.

Offering a weight capacity of up to 50 lbs (22.7 kg), this sliding rack shelf features a ventilated, cold-rolled steel construction for increased airflow and durability in your server room or wiring closet installations.

For ease in routing cables neatly through your rack, we've included a reversible cable management arm that can be attached to the back of the shelf, plus an adjustable bezel to keep your equipment where you want it on the shelf.

Backed by a StarTech.com 2-year warranty.

## Certifications, Reports and Compatibility

## Applications

- Supply additional storage space for hardware or non-rackmount equipment and peripherals
- Install into virtually any standard 4-post rack or cabinet

## Features

- Supports up to 50lbs (22.7kg)
- Adjustable mounting depth from 27.7in (702.2mm) to 31.6in (802.2mm)
- TAA compliant for GSA Schedule purchases
- Includes a reversible cable management arm
- Vented shelf for increased airflow
- Sliding rails with locks to prevent the shelf from sliding out too far
- Sturdy, 2mm cold-rolled steel construction

---

#### Hardware

Warranty	2 Years
U Height	2U
Cable Management	Yes
Industry Standards	EIA RS310-D
Mounting Options	Front Mount (Front and Rear)

---

#### Performance

Weight Capacity (Stationary)	50.1 lb [22.7 kg]
------------------------------	-------------------

---

#### Physical Characteristics

Color	Black
Material	Steel
Rail Thickness	0.1 in [2 mm]
Product Length	0.0 in [0.0 mm]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	18.2 lb [8.2 kg]
Maximum Mounting Depth	31.6 in [80.2 cm]
Minimum Mounting Depth	27.6 in [70.2 cm]



---

**Packaging  
Information**

Package Length	29.5 in [75.0 cm]
Package Width	21.6 in [54.8 cm]
Package Height	4.7 in [12.0 cm]
Shipping (Package) Weight	22.3 lb [10.1 kg]

---

**What's in the  
Box**

Included in Package	Shelf Assembly
	Ear Hook and Slide Assembly (Left / Right)
	Ear Hook Bracket (Left / Right)
	Cable Management Assembly
	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

