

40VMax Vacuum Cleaner Brushless XGT®

CL004G

Model CL004G is a Vacuum Cleaner with an integrated cyclone system.

Equipped with an electric rotary brush the cleaner offers enhanced debris removal performance and maneuverability for cleaning carpets. Main features and benefits: Switch: one touch push button, Dust collection system: Cyclone type, 4-mode suction power selection with mode memory function.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Air volume	1,0 m³/min
Max. sealed suction	200 mbar
Suction power	20 / 40 / 70 / 110 W
Continuous use XGT® 40Vmax / 2.5 Ah	60 / 40 / 20 / 14 min
Tank Capacity for Dust	0,25 L
Product net weight	1,5 kg
Tool weight with battery	1,6 - 2,2 kg
Product Dimensions (L x W x H):	1094 x 243 x 192 mm
Brushless Motor	✓

User benefits

- Lightweight for reduced operator fatigue
- 4 modes with memory function
- Built-in LED light illuminates the work area
- Ergonomic soft grip handle provides increased comfort



Related products

Other

User manual

Parts drawing