

Bourdon Tube Pressure Gauges, Stainless Steel

Modelcode type: 23X.50

Item number: 82452153

Description	
Design	EN 837-1
Nominal size	100 mm
Accuracy class	class 1.0
Scale range	0...6 MPa
Unit of outer Scale	MPa
2nd Scale or Special Scale	2nd scale psi
Process connection	1/4 NPT
Connector location	lower back mount
Materials	
Measuring system	stainless steel
Movement	
Dial	Aluminum, white
Pointer	aluminium, black
Case material	Stainless steel 1.4301
Window	laminated safety glass
Bezel ring	cam ring (bayonet type), stainless steel
Case filling fluid	prepared for filling
Operating conditions	
Permissible medium temperature	+ 200 °C
Permissible ambient temperature	-40 ... +60 °C
Ingress protection	IP 65
Options	
Special design features	oil and grease free
Mounting flange/bracket	front flange, stainless steel
Labelcode	
Label	WIKA standard without / with Tag-number
language of the label	German