

182.72.104.66511 Axial-Rillenkugellager

Axial deep groove ball bearings

51109 (Series 511)

main dimensions to DIN 711/ISO 104, single direction,
separable

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue selection system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	45 mm
D	65 mm
T	14 mm
D ₁	47 mm
d ₁	65 mm
D _a max	53 mm
d _a min	57 mm
r _a max	0,6 mm
r _{min}	0,6 mm
m	0,087 kg Mass
C _a	26500 N Basic dynamic load rating, axial
C _{0a}	69000 N Basic static load rating, axial
A	0,025 Minimum load factor
n _G	7100 1/min Limiting speed
n _B	5800 1/min Reference speed
C _{ua}	3050 N Fatigue limit load, axial

