



Product data sheet

Power tools for trade & industry

Radio

PRO GPB18V-3SC



Great sound to carry around: flexible and portable digital jobsite radio

The most important data

Battery voltage	18.0 V
Radio frequency range FM	87.5 – 108 MHz

Part Number 0 601 4A3 300

Technical data

Technical data

Radio frequency range FM	87.5 – 108 MHz
Radio frequency range DAB+	174.928 – 239.2 MHz
Station presets FM	4
Station presets DAB+	4
Weight excl. battery	2.1 kg
Packaging dimensions (width x length x height)	190 x 370 x 165 mm
Battery voltage	18.0 V
Bluetooth® type	Bluetooth 5.4
Charge level indicator	Yes
External power supply included	No
Hook	Yes
IP protection type	IP54
Max. USB charging current	1.5 A
Multi-Speaker Sound	Yes
Nominal output per mid-range speaker	10 W
No of USB charging ports	1
Number of speakers	2
Playing music via USB	No
USB charging	Yes
Subwoofer	No
Radio source	FM, DAB+

Bluetooth®	Yes
USB Input Type external power supply	USB-C

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Enjoy great sound via DAB+, Bluetooth®, FM, and Multi-Speaker Sound
- Handle and hook for vertical and horizontal placement and for easy storage and transportation
- Share and connect music streams via Bluetooth® on multiple compatible devices with Multi-Speaker Sound

**HEAVY
DUTY****PROFESSIONAL
18V
SYSTEM**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

