

SMD tweezers set 6 pcs

Art.-No.	5-050
Description	SMD tweezers set 6 pcs
Application	Electronics, placement tweezers, SMD/THT precision tweezers
Specification	Dimensions see data sheets individual articles (pictogram)
Material	stainless steel
Surface/Coating	matt finish
Features	stainless, antimagnetic, acid-resistant
Surface resistance	/
Total length	measures 130 × 140 × 20 mm
Weight	weight 135 g

Application and technical data

Tweezers for SMD/THT technology, for gripping parts and components such as mini MELFs, diodes, resistors or precise pick-up of filigree wires.

100% stainless steel anti-magnetic, rustproof and acid-resistant, reflection-free matt fine polished. Stainless austenitic chromium nickel quality steel with low carbon content, for good corrosion resistance (not seawater resistant).

Case consisting of ESD imitation leather, EPA suitable for electrostatically protected areas (ESD workplace/ESD protection zone corresponds to standard DIN EN 61340-5-1), dissipative 10^6 Ohm. The leatherette is flame retardant, biocompatible and contains a dissipative Velcro strap to prevent static charge when opening.

Parts list

SMD tweezers set consists of:

5-050-0 leatherette bag 6 empty pockets

5-051 SMD tweezers 120 mm form 2 stainless steel

5-052 SMD tweezers 110 mm form 5b stainless steel angle 30°

5-054 SMD tweezers 120 mm form 7abb stainless steel very pointed

5-058 cross tweezers 120 mm form 53c stainless steelfself-locking

5-061 SMD tweezers 115 mm form 2ab stainless steel angle 30°

5-062 SMD tweezers 115 mm form 59 stainless steel angle 35°

