

Data sheet

Commercial Art.No.: 83.040.0000.0

IP switch WIENET UMS 6

wieNET IP Switch, 6 TP-RJ45-Ports, transfer rate 10/100 MBit/s, unmanaged switch, Autonegotiation, Autosensing, Autocrossing-function, redundant power supply, supply voltage: 9-30 V, vertical mount

1011011010001010010101101
0100110110010110100101010
101001101100111001010010
10101001101100111001010010
10101001101100111001010010
1101010011011001011010010
1010101010010101101010011

**DIGITALIZATION
IN PROGRESS**

Commercial Art.No.	83.040.0000.0
EAN	4049088081927
Order Unit	1

Certificates / Approvals



Technical data

Allgemein

Mounting method	DIN rail (top hat rail)
Degree of protection (IP)	IP50
Housing material	Metal
Manageable	No
Ethernet	Yes
Power over Ethernet	No
Fast Ethernet	Yes
Gigabit Ethernet	No
Number of ports 10/100 Mbps RJ45	6
Diagnostic LEDs	Power/Link status/Data/Data rate
10 Gigabit Ethernet	No
Number of ports 10/100/1000 Mbps RJ45	0
Number of ports 100 Mbps SC	0
Number of 100 Mbps ST-Ports	0

Technical data

Voltage type	DC
Min. operating temperature	-10 °C
Max. operation temperature	60 °C
Redundant power supply	2 power inputs

Supply circuit

Voltage type	DC
Operating voltage min.	9 V
Operating voltage max.	30 V

Dimensions

Depth	80 mm
-------	-------

Width	45.3 mm
Height	90 mm

Classification

ECLASS 8.1	19170106
ETIM 7.0	EC000734
ETIM 6.0	EC000734
ETIM 5.0	EC000734
ETIM 4.0	EC000734
ETIM 3.0	EC000734