

## Features

- Non-conductive
- Anti-magnetism
- Nylon lock body
- Nylon shackle

## RS PRO Padlocks

RS Stock No.: 0217691



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

*Nylon lock body and nylon shackle combined perfectly, with better non-conductive, anti-magnetism quality.*

*Nylon shackle is non-conductive, especially suitable for military, mining and power areas.*

*Lock body dimensions: Length 45mm, Width 40mm, Thickness 19mm, Shackle Diameter 4mm, Shackle Height 38mm.*

*Include 2 sets lock body warning labels, where you can write the owner's information.*

## General Specifications

Lock Type	Key
Material	Nylon
Bluetooth	No
Keyed Alike	Keyed to differ
Indoor/Outdoor	Indoor
Weather Proof	No
Colour	Red
Quantity Per Package	1
Packaging Type	Box
Body Shape	Square
Shackle Shape	U
Shackle Material	Nylon
Key Retaining	Yes

## Mechanical Specifications

Shackle Length	38mm
Body Width	40mm
Shackle Diameter	4mm
Body Thickness	19mm
Vertical Shackle Clearance	38mm

Horizontal Shackle Clearance	22mm
Overall Width	40mm
Body Height	87mm
Weight	67.5g

## Approvals

Compliance/Certifications	CE
---------------------------	----