



Datasheet

RS PRO Digital TOSLINK Audio or Coaxial to R/L Analogue Converter, Black


Stock number: 2299940


EN

The RS PRO digital TOSLINK or coaxial to analogue audio converter has a black metal shell.

The inputs available are TOSLINK and coaxial which the converts to left and right RCA outputs. It supports sampling rate of 32, 44.1, 48 and 96 KHz and 24-bit S/PDIF incoming bit stream on left and right channels.

This converter could be used with a TV with TOSLINK audio out to a sound bar with analogue left and right RCA input.







Signal Inputs/Output	
Input Audio	Coaxial or Toslink digital audio
Output Audio	L/R audio
Connector	
Input audio connector	Toslink、1XRCA(Coaxial)
Output audio connector	2XRCA (R/L)
Sampling rate	32, 44.1, 48 and 96 KHz
Mechanical	
Size(L-W-H)	51X41X26MM
Weight (Net)	78g
Warranty	
Limited Warranty	1 Year Parts and Labor
Environmental	
Operating Temperature	0 °C to +45°C
Operating Humidity	10% to 85 % RH (no condensation)
Storage Temperature	-10°C to +80°C
Storage Humidity	5% to 90 % RH (no condensation)
Power Requirement	
External Power Supply	5V DC@2A
Power Consumption	0.5 watts (max)