

Datasheet

Stainless Steel Threaded Fitting Straight Bulkhead Adapter, 1/4 in G Female

RS Stock Number [4586823](#)



Features

- Male to female bulkhead adaptor
- Stainless steel construction features excellent chemical resistance to aggressive fluids and environments.

Specifications

- | | |
|-----------------------------|------------------|
| • Connection 1: | 1/4 in G Female |
| • Connection Gender 1: | Female |
| • Fitting Direction: | Straight |
| • Fitting Type: | Bulkhead Adapter |
| • Thread Size 1: | 1/4in |
| • Thread Standard 1: | G |
| • Maximum Working Pressure: | 150 bar |
| • Working Temperature: | 20 to 180 °C |
| • Body: | Stainless Steel |

Measurements

- | | |
|-----------------|-------|
| • C : | G1/4 |
| • F (mm): | 24 |
| • F1 (mm) | 27 |
| • Kmaxi (mm) | 15 |
| • L (mm) | 21 |
| • L1(mm) | 4 |
| • ØT mini (mm): | 20.5 |
| • Weight (kg): | 0.053 |

