



Datasheet

ENGLISH

PID Temperature Controller, 77 x 35mm, 24 V dc, 24 V ac Supply Voltage

RS Stock number 7983505



Features

4 Digits display

- Easily adjustable from front panel
- Configurable display scale between -1999 and 9999
- Adjustable decimal point
- Selectable universal process Input (0-10 V, 0-1 V, 0-60 mV, 0-20 mA -20 mA)
- Adjustable input filter
- Maximum and minimum measurement value are registered to the devices memory
- Maximum or minimum measurement value can be shown continuously on the display
- User can be adjust device's reading value for selected input type
- Alarm output

Relay or SSR driver output (It must be determined in order.)

- Adjustable alarm set value from front panel
- Programming mode password protect