RS PRO Standard Lockout Hasp with Key Storage - 9 Holes

RS Stock No.: 0802197



Features

- Heavy-duty lockout hasp with integrated key storage system.
- Built-in compartment securely stores up to 4 keys during maintenance
- 38mm jaw opening suitable for standard industrial isolation points.
- Scissor-action mechanism ensures smooth operation and secure locking.
- Accommodates up to 9 padlocks (max 9 mm shackle diameter).
- Red powder-coated steel body provides durability and high visibility.
- Warning label enhances safety communication and compliance.
- Ideal for multi-operator lockout and team-based maintenance tasks.

RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- ***Integrated Key Storage Compartment*** *- Innovative design includes a* ***built-in key storage chamber****, securely holding up to* ***4 padlock keys****, preventing key loss and reducing unauthorised access risks during maintenance.*
- ***High-Capacity Group Lockout*** *- Accepts up to* ***9 padlocks*** *with shackle* ***diameters up to 9 mm****, making it ideal for large maintenance teams and multi-person lockout procedures.*
- ***38 mm Jaw Size with Scissor-Action Mechanism*** *- Features a* ***38 mm inner jaw diameter*** *and smooth scissor action for reliable, secure engagement on isolation points.*
- ***Heavy-Duty Steel Construction*** *- Manufactured from* ***durable steel,*** *ensuring strength, mechanical reliability, and long-term industrial performance.*
- ***Corrosion-Resistant Red Powder Coating*** *- Finished with a* ***high-visibility red powder coating,*** *offering excellent resistance to corrosion, abrasion, and harsh industrial environments.*
- ***Clear Safety Identification*** *- Supplied with a* ***bold, high-visibility warning label*** *to clearly indicate locked-out status and support compliance with LOTO procedures.*
- ***Ideal for Large Maintenance Teams*** *- Designed specifically for group lockout scenarios where multiple personnel must secure the same energy isolation point.*

General Specifications

Type	Lockout Hasp
Material	Mild Steel
Colour	Red
Padlock holes	9
Package	PE-LD

Mechanical Specifications

Dia (Jaw Size)	38mm
Width	60mm
Height	199mm
Depth	38mm
Accepts Shackle Dia	9mm
Weight	250 Grams

Operation Environment Specifications

Withstand temperature	-20°C to 90°C

