


E70600



AS-Interface power distributor

QUAD AS-i Splitter Box 8A



Application

Design AS-i / 24 V

Electrical data

Operating voltage [V] 26.5...31.6 DC

Max. current load total [A] 8

Additional voltage supply [V] 24 DC

Operating conditions

Ambient temperature [°C] -25...75

Protection IP 65

Mechanical data

Weight [g] 89.5

Materials PA 6.6; screws: stainless steel (316L/1.4404); Nuts: stainless steel (316L/1.4404); flat cable seal: NBR

Remarks

Pack quantity 1 pcs.