
Parker Product Datasheet



Quick coupling system with nominal diameter 2.7 for pneumatic, liquids and gas applications up to 35 bar. Available in nickel-plated brass or stainless steel.

PART NUMBER: 20SFKO04RXX
CONNECTION SIZE: 3x4 MM
COUPLING HALF: Plug
CONNECTION TYPE: Tube
BODY MATERIAL: Stainless Steel 303
FUNCTION: Straight-Through

PRODUCT OVERVIEW

Parker’s Series 20 is a mini-industrial coupling with European profile. Coupling system with single-hand operation. High flow rate despite small dimensions.

Markets:
- Industrial
- Life Sciences
- Medical technology
- Chemistry pharmacybr/>- Electronics and energy management
- Transportation
- Machinery construction
- Automotive
- Process

Features/Benefits:

- Mini Industrial coupling
- Single hand operation for easy and fast connection
- European profile is the most representative profile worldwide

TECH SPECIFICATIONS

FOR FLUID TYPE	Chemicals (Paints, solvents, lubricants)
DIAMETER	2.7 mm (nominal)
FOR FLUID TYPE	Water (Industrial, drinking, treated water)
FOR FLUID TYPE	Coolants (Industrial coolants, water-glycol)
BODY MATERIAL	Stainless Steel 303
MAXIMUM OPERATING TEMPERATURE	240 °C
MINIMUM OPERATING TEMPERATURE	-40 °F
APPLICATION	Medical
MINIMUM OPERATING TEMPERATURE	-40 °C
MAXIMUM OPERATING PRESSURE	35 bar
APPLICATION	Food & Beverages
DIVISION	Low Pressure Connectors Europe Division
COUPLING HALF	Plug
CONNECTION SIZE	3x4 mm
LENGTH	25 mm
APPLICATION	Pharma
PLATING TYPE	Without Surface Treatment
DIVISION	Low Pressure Connectors Europe Division
MAXIMUM OPERATING TEMPERATURE	464 °F

MAXIMUM OPERATING PRESSURE	507 psi
APPLICATION	Industrial Machinery
VALVE TYPE	Without Valve
SEAL MATERIAL	Without Seal
BRAND	Rectus
APPLICATION	Energy Management
HEX SIZE	8 mm (external)
TECHNOLOGY	Fluid & Gas Handling
OPERATION TYPE	No Sleeve
INDUSTRY	Electronics
COMPATIBLE FITTING	Series 20 Coupler
VALVE INCLUDED	No
FUNCTION	Straight-Through
QUANTITY PER BOX	2.0
INTERCHANGE TYPE	European Profile
CONNECTION TYPE	Tube With hose nut, without spring guard
SLEEVE MATERIAL	Without Sleeve
FLOW RATE	165 L/min (air)
PRODUCT SERIES	Series 20
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air, inert gases)
FLOW RATE	1.5 L/min (water)
INDUSTRY	Healthcare & Life Sciences
WEIGHT	0.004 kg
INDUSTRY	General Industrial
PRODUCT STYLE	Quick Connect
BRAND	Parker

APPLICATION	Electronics
PRODUCT TYPE	Pneumatic Quick Couplings
TECHNOLOGY	Pneumatics
REGION OF ORIGIN	Germany