

# Eaton 12AKGH0125

Catalog Number: 12AKGH0125

Air fuse-link, medium voltage, 125 A, AC 12 kV, 76 x 359 mm, back-up, BS, with striker, O-version

General specifications



Product Name	Catalog Number
Eaton Bussmann series medium voltage BS air fuse	12AKGH0125
	EAN
	5027590430593
Product Length/Depth	Product Height
359 mm	76.2 mm
Product Width	Product Weight
76.2 mm	4029 g
Compliances	
CE Marked	
RoHS conform	

## Product specifications

## Resources

### Type

Fuse

### Application

protection of primary side  
transformers  
used in fuse switch  
combination units, fuse  
bases and fuse switches

### Amperage Rating

125 A

### Fuse indicator

With Striker

### Fuse size

76 x 359 mm

### Breaking capacity

20 kA

### Installation technique

Air

### Performance Cat According To IEC 60282-1

Back-up

### Product application

Primary side transformer protection

### Rated frequency - max

50 Hz

### Rated frequency - min

50 Hz

### Release characteristic

Other

### Standard

British Standard

### Utilization category

Other

### Voltage type

AC

### With striker

Yes

#### Class

Class back-up

#### Fuse shape

Cylindrical, offset bolted tags

#### Fuse diameter

76 mm

#### Interrupt rating

20 kAIC

#### Construction size

76 x 359 mm

#### Mounting method

Clip-in

#### Voltage rating

12 kV

#### Fuse type

AKGH



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)