



tesa® 4671

Product Information



Colored gaffer tape

Product Description

tesa® 4671 is an adhesive tape designed with a woven rayon fabric backing and a natural rubber adhesive. It is the premium gaffer tape in the assortment for stages, fairs and exhibitions with corresponding applications.

Available in 8 colors: black, white, grey, red and also fluorescent neon colors: pink, orange, yellow and green.

Sustainable Aspects

- 51% bio-based carbon content (DIN EN 16640)



For more information: <https://www.tesa.com/product-sustainability>

Product Features

- High adhesion even on rough surfaces
- Can be removed without leaving any residues from almost any surface
- Available in reflective and appealing neon colors
- Solvent-free production processes

Application Fields

Suitable for several applications in the event sector such as

- Gaffer work during exhibitions
- Marking of positions on stage
- Covering sharp edges
- Suitable for indoor applications

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|----------------------|---|--------|
| • Backing | Acrylic-coated cloth | • Bio-based carbon content (DIN EN 16640) | 51 % |
| • Type of adhesive | natural rubber | • Total thickness | 280 µm |

For latest information on this product please visit <http://l.tesa.com/?ip=04671>



tesa® 4671

Product Information

Properties/Performance Values

• Elongation at break	9 %	• Mesh	120 count per square inch
• Tensile strength	70 N/cm	• Straight tear edge	very good
• Abrasion resistance	very good	• Temperature resistance	140 °C
• Easy to write on	yes	(removability from aluminum after 30 min exposure)	
• Hand tearability	very good	• Water resistance	good

Adhesion to Values

• Steel	3.8 N/cm
---------	----------

Additional Information

Recommendation: please conduct a test on the application surface before using the product.

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?ip=04671>