## **SIEMENS**

## **Data sheet**

6ES7972-0BB42-0XA0

## product type designation

product description



## **PROFIBUS** connector

PROFIBUS bus connector, RS 485, screw, with programming port, 35°

SIMATIC DP, Connection plug for PROFIBUS up to 12 Mbit/s with inclined cable outlet, 15.8x 54x 39.5 mm (WxHxD), terminating resistor with isolating function, With PG receptacle

suitability for use	For connecting PROFIBUS stations to the PROFIBUS bus cable
transfer rate	
transfer rate / with PROFIBUS DP	9.6 kbit/s 12 Mbit/s
interfaces	
number of electrical connections	
• for PROFIBUS cables	2
<ul> <li>for network components or terminal equipment</li> </ul>	1
type of electrical connection	
<ul> <li>for PROFIBUS cables</li> </ul>	Screw
<ul> <li>for network components or terminal equipment</li> </ul>	9-pin sub D connector
type of electrical connection / FastConnect	No
mechanical data	
design of terminating resistor	Resistor combination integrated and connectable via slide switch
material / of the enclosure	plastic
locking mechanism design	Screwed joint
design, dimensions and weights	
type of cable outlet	35 degree cable outlet
width	15.8 mm
height	54 mm
depth	39.5 mm
net weight	34 g
ambient conditions	
ambient temperature	
<ul> <li>during operation</li> </ul>	-25 +60 °C
during storage	-40 +70 °C
during transport	-40 +70 °C
protection class IP	IP20
product features, product functions, product components / general	
product feature	
• silicon-free	Yes
product component	
<ul> <li>PG connection socket</li> </ul>	Yes
strain relief	Yes
standards, specifications, approvals	
certificate of suitability	
<ul> <li>RoHS conformity</li> </ul>	Yes
UL approval	Yes
reference code	

according to IEC 81346-2 XG

further information / internet links

internet link

 to website: Selection guide for cables and connectors

https://sie.ag/2QdlxcP

last modified: 8/16/2023 🖸