

Technical specs

M6PAN - M6PAN

Name:

POLYESTER COTTON PANOSTYLE® WORKING TROUSERS

Size:

XS - S - M - L - XL - XXL - XXXL

Colour:

Brown - Grey - Navy Blue



Description :

PANOSTYLE® working trousers 65% polyester / 35% cotton. Elasticated waist on both sides. 5 pockets.

Materials:

65% polyester 35% cotton 235 g/m²

Instructions for use:

PANOSTYLE range protection clothing protecting users against superficial mechanical effects only against minor risks, with no chemical, electrical or heat risks. Designed for general use.

Limits to use:

Do not use other than for the purpose defined in the instructions for use below. Before donning this garment, check that it is not dirty or worn, as this would lead to a loss of its effectiveness. Wear it closed. This garment contains no known carcinogenic or toxic substances, or substances which may cause allergies in sensitive people.

Instructions for storage:

Store in its original packaging away from light and humidity.

Instructions for cleaning / maintenance:

Maximum washing temperature 60°C, normal mechanical treatment, rinse at normal temperature, normal spin. Do not bleach. Iron at a maximum temperature of 150°C Do not dry clean, do not use stain-removing solvents. Tumble drying possible. Moderate programme at low temperature.

Performances :

Compliant with the essential requirements of the Directive 89/686/EEC and the general requirements of the standard EN340:2003

TESTS RESULTS:

- Dimensional variations (NF EN 25077:2007 - ISO 6330:2002): after 5 domestic washes at 60°C + free air drying : Compliant (+/-3%) ;
- Tensile strength according to EN ISO 13934-1: Warp direction > 200 daN / Weft direction > 100 daN
- Perpendicular tear force according to EN ISO 13937-2: Warp direction > 30N / Weft direction > 30N
- Abrasion resistance according to EN530 (method 2) & EN ISO 12947-2 : > 50 000 cycles



DELTA PLUS GROUP

La Peyrolière - B.P. 140 - 84405 APT Cedex - France
www.deltaplus.fr



UPDATE : 25/03/2010