



Datasheet

ENGLISH



RS 811-7070

Basic Vertical PDU with:-

- 16 x UK BS1363 Right Hand Angled Sockets
- Unit Switch
- EMI Filter
- 3 Metre Bottom Front Fed Lead
- 230V/13A UK BS1363 Plug
- Black Finish

Specifications:

| | |
|---|----------------------------------|
| Quantity Of Inputs | 1 |
| Voltage | 230V |
| Amperage | 13A |
| VA per Input (Load Capacity) | 2.9kW |
| Frequency | 50/60 Hz |
| Over Current Protection | None |
| Switch | Green neon with protective cover |
| Power Cable Wire Gauge | 1.5mm ² PVC |
| Power Cable Length | 3m |
| Plug Type | BS 1363P |
| Receptacle/Socket Type #1 | BS1363 |
| Quantity on Face #1 | 16 |
| Style #1 | Individual - Right Hand Angled |
| Maximum Output per Receptacle/Socket #1 | 13A |
| Voltage per Receptacle/Socket #1 | 230V |
| Heavy Steel -Black Powder Coat | Yes |
| Configuration | 66in / 1682mm Vertical Rackmount |
| GE Vertical Mounting Bracket | Yes |
| Toolless Mounting Hardware - Center to Center Spacing | 1555 mm and 1644mm |
| Product Warranty | Lifetime |
| Certification/Agency Approvals | Complies with EN 60950 |
| Certification/Agency Approvals | RoHS Compliant |
| Certification/Agency Approvals | CE Marked |
| Chassis Dimensions (LxWxD) | 1682mm x 54mm x 51mm |