

7221 // ULTIMATE STEP HIGH FIT

Boots
PPE risk category II



Waterproof and breathable SECONAMICS membrane
Well padded bootleg for optimal fit and comfort
TPU reinforcement at heel



S7S

CI

FO

SC

SR



SECONAMICS



7221 // ULTIMATE STEP HIGH FIT



Shoe upper:	Action Leather, black TPU, black
Outsole:	PU / TPU, black / transparent
Size(s):	36-48
Packaging unit:	5 pair(s)
Certification:	EN ISO 20345, EN IEC 61340-4-3

NITRAS ULTIMATE STEP HIGH FIT, safety boots, high, S7S CI FO SC, durable Action Leather, black, durable PU / TPU outsole, black / transparent (colour code: 1000), fibreglass toe cap, textile perforation resistant midsole, metal-free, premium COMFORT STEP insoles, ergonomically formed, with dial fastener 711 // FIT SYSTEM for fast availability and optimal fit, waterproof and breathable SECONAMICS membrane, highest slip resistance (SR), width 11, well padded bootleg for optimal fit and comfort, reflective elements, heel lining for easy donning and doffing and heel reinforcement made of robust microfibre, additional toe cap, TPU reinforcement at heel, premium quality, DGUV Rule 112-191-proofed, Type 1, ESD-capable, PPE risk category II

EN ISO 20345

EN IEC 61340-4-3



S7S

CI

FO

SC

SR



SECONAMICS



786

Industries

-  Craft
-  Building / Construction
-  Landscape gardening
-  Transport / Logistics
-  Waste management
-  Refrigeration range

Advantages

- + Waterproof and breathable SECONAMICS membrane
- + Well padded bootleg for optimal fit and comfort
- + TPU reinforcement at heel



Further images



Additional information

Miscellaneous

Weight 786

Logistics data

Size	GTIN (SPU)	GTIN (PU)	Length (m)	Width (m)	Height (m)	Weight (kg)	Quantity PU / pallet
36	4059904208018	4059904208148	0,645 m	0,335 m	0,375 m	7,5 kg	16
37	4059904208025	4059904208155	0,645 m	0,335 m	0,375 m	7,85 kg	16
38	4059904208032	4059904208162	0,645 m	0,335 m	0,375 m	8,2 kg	16
39	4059904208049	4059904208179	0,645 m	0,335 m	0,375 m	8,55 kg	16
40	4059904208056	4059904208186	0,645 m	0,335 m	0,375 m	8,9 kg	16
41	4059904208063	4059904208193	0,645 m	0,335 m	0,375 m	9,25 kg	16
42	4059904208070	4059904208209	0,645 m	0,335 m	0,375 m	9,6 kg	16
43	4059904208087	4059904208216	0,67 m	0,375 m	0,41 m	9,95 kg	16
44	4059904208094	4059904208223	0,67 m	0,375 m	0,41 m	10,3 kg	16
45	4059904208100	4059904208230	0,67 m	0,375 m	0,41 m	10,65 kg	16
46	4059904208117	4059904208247	0,67 m	0,375 m	0,41 m	11 kg	16
47	4059904208124	4059904208254	0,67 m	0,375 m	0,41 m	11,35 kg	16
48	4059904208131	4059904208261	0,67 m	0,375 m	0,41 m	11,85 kg	16

Customs tariff number: 64039113900

Country of origin: China