

Product Data Sheet

MaxiFoam® 34-800

Colour – Coating	Grey
Colour – Liner	White
Design	Palm coated knitwrist
Coating	NBR (Nitrile Butadiene Rubber)
Coating texture	Micro-Foam for Controlled Grip
Liner	Nylon
Palm thickness	1.10 mm



Dimensions

Size Range	Size 5 (XXS)	Size 6 (XS)	Size 7 (S)	Size 8 (M)	Size 9 (L)	Size 10 (XL)	Size 11 (XXL)
Total glove length (+/-10 mm)	185	200	205	220	235	240	245
Wrist length (mm)	55	65	65	70	70	70	70
Wrist width (mm)	70	70	70	75	75	80	80
Palm width (+/-3 mm)	78	85	87	90	97	100	103
Over lock colour	Purple	Blue	Red	Orange	White	Yellow	Black

EN test Results

Test	Notified Body	Result/Pass
EN ISO 21420: 2020	TÜV Rheinland	Yes
EN 388: 2016 + A1: 2018	TÜV Rheinland	4121A



Product Data Sheet

MaxiFoam® 34-800

Typical Performance Values

EN ISO 21420 Dexterity	Level 5
EN 388:2016 + A1:2018 A. Abrasion Resistance	> 8000 Cycles
EN 388:2016 + A1:2018 B. Cut Resistance	> 1.2 index
EN 388:2016 + A1:2018 C. Tear Resistance	> 25 newtons
EN 388:2016 + A1:2018 D. Puncture Resistance	> 20 newtons
EN 388:2016 + A1:2018 E. Cut Resistance ISO	≥ 2 Newton

HandCare®

Skin Health Alliance Dermatologically Accredited	Yes
REACH compliant	Yes
Standard 100 by OEKO-TEX® (08.BH.57867)	Certified
Washable	40°
Sanitized®	Yes



Special features

Silicone free	Yes
---------------	-----

Packaging

Pairs per poly bag	12
Carton count	144
Carton dimensions (mm)	500 x 295 x 270



Product Data Sheet

MaxiFoam® 34-800

Weight

Size Range	Size 5 (XXS)	Size 6 (XS)	Size 7 (S)	Size 8 (M)	Size 9 (L)	Size 10 (XL)	Size 11 (XXL)
Glove weight / Pair (+/- 6 gram)	28	32	34	40	44	48	52
Gross Weight (Kg)	5.3	5.9	6.2	7	7.6	8.2	8.8
Carton Weight (Kg)	1	1	1	1	1	1	1
Net Weight (Kg)	4.3	4.9	5.2	6	6.6	7.2	7.8

Issue date: 09.07.2018

