

Features

- *Conductor*
Material: 100% copper wires
- *Jacket Material:*
PVC, black
- *Cable Length:* 6M
- *Easy to install and reliable connection*
- *Color:* Black

RS PRO Telephone Cable

RS Stock No.: 0707859



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against

demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This is a RJ12 6P6C to 12 6P6C data cable (also called RJ11 6P6C Cable) for both data and voice use, overall length is 6M. Both ends are durable RJ12 6P6C modular connector. Straight-through pin out for both data and voice use. 100% copper 6 conductor black wire. It can be used as a regular telephone cord, fax cable, DSL modem cable, cash drawer cable and also in printer systems, radio systems and control systems etc

General Specifications

<i>Number of Strands</i>	<i>6</i>
<i>Conductor Strand Type</i>	<i>Stranded</i>
<i>Terminated/Unterminated</i>	<i>Terminated; Unterminated</i>
<i>Connector Type</i>	<i>Male RJ12</i>
<i>Connector B</i>	<i>Male RJ12</i>
<i>Connector A</i>	<i>Male RJ12</i>
<i>Outer Sheath Material</i>	<i>PVC;</i>
<i>Sheath Colour</i>	<i>Black</i>
<i>Conductor Material</i>	<i>Bare Copper</i>
<i>Drain Wire</i>	<i>No</i>
<i>Fire Behaviour</i>	<i>Flame Retardant.</i>

Mechanical Specifications

<i>Length</i>	<i>6m</i>
<i>Outer Diameter</i>	<i>2.4*6.8mm</i>
<i>Sheath Thickness</i>	<i>0.6mm</i>

<i>Insulator Diameter</i>	0.9mm +/-0.05
<i>American Wire Gauge</i>	28AWG
<i>Cross Sectional Area</i>	0.079mm ²
<i>Size of Strands</i>	7/0.12mm, 28AWG
<i>Core Strands</i>	7/0.12mm

Approvals

<i>Compliance/Certifications</i>	RoHS, Reach
<i>Declarations</i>	RoHS, Reach

