




Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 293593-1
NECTOR M PIN 0DEG PCB 3P CODE A

Customers Also Bought



TE Part #2176346-4
CRGCQ 1210 3R3 5%



TE Part #2329383-6
PB OFF/ON FC BLK M2 TERM. IP68



TE Part #3-1879314-3
DPL12S 24P NDET 25K RD/GRN



TE Part #1969804-1
04P UMNL HDR ASSY, SCKT V0 GW



TE Part #4-1418469-1
6POS,AMP MCP1.5K,REC. HSG,CODD



TE Part #1625892-5
3W SM M/OX 5% R47



TE Part #4-2176058-8
RLP73K 3A R91 5% 2K RL



TE Part #293605-1
NECTOR M SKT 0DEG PCB CONN 3P CODE A



TE Part #293602-1
NECTOR M SKT 90DEG PCB CONN 3P CODE A



TE Part #293593-1
NECTOR M PIN 0DEG PCB 3P CODE A

Documents

Product Drawings

NECTOR M PIN 90DEG PCB 3P CODE A

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_293590-1_F_c-293590-1-f.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_293590-1_F_c-293590-1-f.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_293590-1_F_c-293590-1-f.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

[Agency Approval Document](#)

English