



FLIR C3[®]

Powerful, Compact Thermal Imaging System

The FLIR C3 is a full-featured, pocket-sized thermal camera designed to be your go-to tool, whether your work is building inspections, facilities maintenance, HVAC, or electrical repair. Keep it on you so you're ready anytime to find hot fuses, cold air leaks, plumbing issues, and more.

The C3's must-have features include MSX[®] real time image enhancement, area maximum or minimum temperature measurement, and Wi-Fi connectivity – so you can quickly get to the job of finding hidden problems, sharing images, and documenting repairs.

POCKET PORTABLE – PRO FEATURES

Slim and sturdy enough to keep in your pocket, but with the advanced features you need to find potential problems, confirm repairs, and share the evidence with your client or boss.

- Light, slim profile fits comfortably in any work pocket
- Brilliant 3" intuitive touch screen with auto orientation for easy viewing
- Wi-Fi enabled for instant peer-to-peer image sharing
- Area measurement box measures hottest or coldest spot (max./min.)

FULLY RADIOMETRIC

Save thermal image JPEGs instantly, then conveniently adjust and analyze them later with FLIR Tools to isolate temperature measurements on any pixel and create convincing reports.

- MSX[®]-enhanced thermal images provide stunning detail to help you identify problem areas easier
- Radiometric image stores 4800 pixels capable of capturing thermal measurements from -10°C to 150°C (14°F to 302°F)
- High thermal sensitivity detects subtle temperature differences common in building applications


EASILY AFFORDABLE

Affordable MSRP helps get this powerful tool into the hands of the people who can use it every day.

- FLIR Tools professional reporting software included – the industry standard in thermal image post analysis
- Streaming video via FLIR Tools, a feature not usually available on low-cost thermal camera systems
- FLIR's unique 2-10 warranty, covering parts and labor for two years and the detector for ten



Upload images to FLIR Tools over Wi-Fi



Area box with Cold Spot demonstrates air infiltration



Area box with Hot Spot demonstrates electrical fuse is active

Specifications

Overview		C3
IR Sensor		80 x 60
Thermal Sensitivity/NETD		< 0.10°C
Field of View (FOV)		41° x 31°
Minimum Focus Distance		Thermal: 0.15 m (0.49 ft) MSX®: 1 m (3.3 ft)
Image Frequency		9 Hz
Focus		Focus free
Spectral Range		7.5 - 14.0 µm
Digital Camera		640 x 480 pixel
Digital Camera Focus		Fixed focus
Image Presentation		
Image Modes		Thermal, visual, MSX®, Picture-in-Picture
Image Gallery		Yes
MSX®		Adds visual details to full resolution thermal image
Color Palettes		Iron, Rainbow, Rainbow HC, Gray
Auto Orientation		Yes
Touch Screen		Yes, capacitive
Measurement & Analysis		
Object Temperature Range		-10°C to 150°C (14°F to 302°F)
Accuracy		±2°C (±3.6°F) or ±2%, whichever is greater, at 25°C (77°F) nominal
Spotmeter		On/Off
Area		Box with max. or min.
Emissivity Correction		Yes; matte/semi-matte/semi-glossy + custom value
Measurement Correction		Emissivity, Reflected apparent temperature
Image Storage and Streaming		
Storage Media		Internal memory, at least 500 sets of images
Image File Format		Standard JPEG with 14-bit measurement data included
Non-Radiometric IR Video Streaming		Yes
Visual Video Streaming		Yes
Communication and Connectivity		
Communication Interfaces		Wi-Fi, USB
Wi-Fi		Peer-to-peer (ad hoc) or infrastructure (network)
USB 2.0		USB Micro-B connector type: data transfer to and from PC
Additional Information		
Battery Type		Rechargeable Li-ion polymer battery
Battery Operating Time		2 hours
Charging System		Charged inside camera
Charging Time		1.5 hours
External Power Operation		AC adapter, 90-260 VAC input - 5 V output to camera
Operating Temperature Range		-10°C to 50°C (14°F to 122°F)
Storage Temperature Range		-40°C to 70°C (-40°F to 158°F)
Weight		0.13 kg (0.29 lbs)
Dimensions		125 x 80 x 24 mm (4.9 x 3.1 x 0.94 in)
System Includes		
Box Contents		Infrared camera, lanyard, pouch, power supply/charger, tripod mount, USB cable, printed documentation

Specifications are subject to change without notice. For the most up-to-date specs, go to www.flir.com



FLIR C3 with Tripod Mount & Carry Pouch

SWEDEN

Instruments Division
FLIR Systems AB
Antennvägen 6
187 66 Täby
Tel. : +46 (0)8 753 25 00
E-mail : flir@flir.com

FLIR Germany

Frankfurt
Tel. +49 (0)69 95 00 900

FLIR France

Torcy
Tel. +33 (0)1 60 37 01 00

FLIR Spain

Madrid
Tel. +34 91 573 48 27

FLIR Russia

Moscow
Tel. + 7 495 669 70 72

FLIR Africa

Johannesburg
Tel. +27 11 300 5622

Benelux

Sales Administration
FLIR Commercial Systems
Luxemburgstraat 2
2321 Meer
Belgium
Tel.: +32 (0) 3665 5100

FLIR Italy

Milan
Tel. +39 (0)2 99 45 10 01

FLIR UK

West Malling
Tel. +44 (0)1732 220 011

FLIR Middle East

Dubai
Tel. +971 4 299 6898

FLIR Turkey

Istanbul
Tel. +90 (212) 317 90 55

www.flir.com
NASDAQ: FLIR

For more information:
flir@flir.com

Equipment described herein is subject to US export regulations and may require a license prior to export. Diversion contrary to US law is prohibited. Imagery for illustration purposes only. Specifications are subject to change without notice. ©2017 FLIR Systems, Inc. All rights reserved. 02/01/2017

16-1751-EMEA